

AquaCrystal

Crystal Clarity Water



Deep Bed for Superior Filtration


W & WD filters are designed with filter depths of 600mm and 1000mm respectively, providing enhanced in depth filtration and increased dirt retention capacity. When dirt is driven through the filter bed, Glass Pearls with its spherical media size between 0.6mm - 0.8mm, traps particles in extremely narrow geometrical spaces, capable of filtering down to 3microns.



Maximum working temperature of 50° C

Safe and Save

Glass Pearls are manufactured from 100% pure glass and are chemically inert. Its spherical size with no sharp edges, making them really safe to use. The superior purity greatly reduces its initial and long term operational backwash duration which enables easy filter start up, as well time and water savings.



Glass Pearl Technical Specification

Property	Specification				
Nominal Product Size	0.61 mm				
Uniformity Coefficient	1.21				
Hardness (Moh Scale)	7.00				
Particle Specific Gravity	2.2/2.3				
Bulk Density	Around 1610kg / m³				

Glass Pearl Chemical Compostions

	-
Property	Specification
Silicon Dioxide (SiO2)	70.00 - 75.00%
Sodium Oxide (Na2O)	12.00 - 15.00%
Calcium Oxide (CaO)	7.00 - 12.00%
Magnesium Oxide (MgO)	Approx. 5.00%
Aluminium Oxide (AL2O3)	Approx. 2.50%
Potassium Oxide (K2O)	Approx. 1.50%

Technical Specification

Model	Filter	Valve Size	Inner Dia.	Filter Area	Bed Depth	Filtration Flow rate				Media	Glass Pearl
						20m³/hr/m²		36m³/hr/m²		Volume	0.6 - 0.8mm
		(mm)	(mm)	(m²)	mm)	(lpm)	(m³/hr)	(lpm)	(m³/hr)	(litres)	(kg)
AC250	W250	40	250	0.05	600	17	1.0	30	1.8	41	66
AC300	W300	40	300	0.07	600	23	1.4	42	2.52	58	93
AC400	W400	40	400	0.13	600	43	2.6	78	4.7	79	127
AC500	W500	40	500	0.20	600	67	4.0	120	7.2	123	198
AC600	W600	40	600	0.28	600	93	5.6	168	10.1	175	282
AC700	W700	40	700	0.38	600	127	7.6	228	13.7	240	386
ACD300	WD300	40	300	0.07	1000	23	1.4	42	2.5	86	138
ACD400	WD400	40	400	0.13	1000	43	2.6	78	4.7	129	208
ACD500	WD500	40	500	0.20	1000	67	4.0	120	7.2	199	320
ACD600	WD600	40	600	0.28	1000	93	5.6	168	10.1	288	464
ACD700	WD700	40	700	0.38	1000	127	7.6	228	13.7	394	634
ACD900	WD900	50	900	0.64	1000	213	12.8	384	23.0	692	1114

OFFICES - AUSTRALIA

NSW - Sydney (Head Office) Tel: +61 2 9898 8600 QLD - Brisbane

Tel: +61 7 3299 9900 VIC/TAS - Melbourne Tel: +61 3 9764 1211

WA - Perth Tel: +61 8 9273 1900 SA/NT - Adelaide Tel: +61 8 8244 6000

ACT Distribution Tel: +61 2 6280 6476

OFFICES - OVERSEAS

Waterco (Europe) Limited Sittingbourne, Kent. UK Tel: +44 (0) 1795 521 733

Waterco (USA) Inc Augusta, Georgia, USA Tel: +1 706 793 7291

Waterco Canada Boucherville, Quebec, Canada Tel: +1 450 748 1421

Waterco (NZ) Limited Auckland, New Zealand Tel: +64 9 525 7570 Waterco (C) Limited Guangzhou, China Tel: +86 20 3222 2180

Waterco (Far East) Sdn Bhd Selangor, Malaysia Tel: +60 3 6145 6000

PT Waterco Indonesia Jakarta, Indonesia Tel: +62 21 4585 1481

Waterco Singapore Intl Pte Ltd Nehsons Building, Singapore Tel: +65 6344 2378

DISTRIBUTED BY:





